

CAT. N° BH1040



FIXED CAPACITOR BANK ALPIBLOC - H TYPE THREE PHASE 400 V - 50 HZ - 10 KVAR

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

H type

Max. harmonic pollution level THDU ≤ 4%, THDI ≤ 15%

- Nominal power : 10 kVAr
- Circuit breaker rating : 20 A
- Breaking capacity : 50 kA

General characteristics

Fixed capacitor banks Alpibloc

- 400 V - 50 Hz three-phase network
- Alpibloc is an Alpivar³ capacitor with built-in circuit breaker
- Assembly fitted and wired in an IP 31 - IK 05 box or cabinet
- Equipment supplied ready for connection, for fixed compensation of low and medium power electrical devices
- For certain applications (remote control, etc.) the circuit breaker can be replaced by a contactor and HRC fuses (on request)
- Conforming to standard IEC 61921

Documentation



Catalogue pages & additional information

- [Description page \(p.116\)](#)



Installation & technical data

- BH1040