


REF . 0 160 40


**HRC BLADE TYPE CARTRIDGE FUSE - CYLINDRICAL
TYPE AM 22 X 58 - 32 A - W INDICATOR**


Emballage (nombre number of units)	3
Volume (dm ³)	0,693
Poids (g)	601,00

Caractéristiques du produit
Type aM (motor rated)

- Conform to EN 60269-1, IEC 60269-1, 2 and VDE 0636-1
- Fully insulated end plate and handle lugs

Size 00

- With indicator
- Rating : 80 Amps
- Voltage ~ : 500 Volts
- Breaking capacity : 120000 Amps

Caractéristiques générales
HRC blade type cartridge fuses - gG/gL and aM types
Documentation associée

Catalogue pages & additional information

- [Description page \(p.180\)](#)
- [Blade cartridge fuses gG and aM types](#)


Installation & technical data

- [F00190EN/06](#)