

CAT. N° 0 163 35



HRC BLADE TYPE CARTRIDGE FUSE - TYPE GG - SIZE 00 - 63 A - WITH INDICATOR

| | |
|---------------------------|----------|
| Pack (number of units) | 10 |
| Volume (dm ³) | 2,066 |
| Weight (g) | 1 971,00 |

Product characteristics

Type gG / gL

- Conform to IEC 60269-2
- For protection against accidental contacts, use terminal shields and fuse covers supplied with protection kits

Size 00

- With indicator
- Rating : 63 Amps
- Voltage ~ : 500 Volts
- Breaking capacity : 120000 Amps

General characteristics

HRC blade type cartridge fuses - gG/gL and aM types

Documentation



Catalogue pages & additional information

- [Description page \(p.180\)](#)
- [Blade cartridge fuses gG and aM types](#)



Installation & technical data

- [F00189EN04](#)