

CAT. N° 0 133 02



## HRC CARTRIDGE FUSE - CYLINDRICAL TYPE GG 10 X 38 - 2 A - WITHOUT INDICATOR

Pack (number of units)	10
Volume (dm <sup>3</sup> )	0,057
Weight (g)	80,00

### Product characteristics

#### Cylindrical type gG

- Conform to EN 60269-1, IEC 60269-1 and 2

#### 10 x 38 HRC

- Without indicator
- Rating : 2 Amps
- Voltage ~ : 500 Volts
- Rupture capacity : 100000 Amps

### General characteristics

#### HRC cartridge fuses

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.179\)](#)
- [Blade cartridge fuses gG and aM types](#)

#### Agreements & certificates of conformity

- [LRS \(Lloyd's\) - 13/00020\(E1\)](#)

#### Installation & technical data

- [F00192EN/06](#)
- [F00192EN-08](#)