

**CAT. N° 0 048 15**

**IP2X TERMINAL BLOCK - NEUTRAL (BLUE) - 1 X 10 TO 35<sup>2</sup>  
- 5 X 6 TO 25<sup>2</sup> - L. 62 MM**

Pack (number of units)	10
Volume (dm <sup>3</sup> )	0,701
Weight (g)	430,00

**Product characteristics**
**Distribution terminal blocks**

- Conform to standard IEC 60998-2-1
- Supplied ready for use (screws not tightened)
- 100 A max. - 400 V~ with 25 mm<sup>2</sup> input
- 80 A max. - 400 V~ with 16 mm<sup>2</sup> input

**IP 2X terminal blocks**

- Mounting on rail with universal support Cat.No 0 048 11, or on 12 x 2 flat bar
- Neutral
- blue
- Number of connections : 1 x 10 to 35 + 5 x 6 to 25 mm<sup>2</sup>
- Length : 62 mm

**General characteristics**
**Distribution terminal blocks**
**Documentation**

**Catalogue pages & additional information**

- [Selection chart \(p.198\)](#)
- [Description page \(p.200\)](#)


**Agreements & certificates of conformity**

- [OC / CB - FR\\_633370/M2](#)