

CAT. N° 0 412 21

**LIDO BELL - SURFACE-MOUNTING 230 V~ - 50/60 HZ - IP20  
- IK04 - CLASS II**

Pack (number of units)	10
Volume (dm <sup>3</sup> )	3,547
Weight (g)	901,00

**Product characteristics****Lido bells**

- IP 20 - IK 04
- Average acoustic output at 1 m: 80 dB at 1 m
- Surface-mounting with screws with levelling facilities

**Class II**

- Double insulated
- 230 V~ - 50/60 Hz
- Dim.: 95 x 61 x 33 mm
- Consumption: : 30 mA
- Average acoustic output at 1 m : : 80 dB

**General characteristics****Bells, bell pushes****Documentation****Catalogue pages & additional information**

- [Description page \(p.647\)](#)