

REF . 6 462 03

**LINKEO FIX 19" CABINET WITH FIX SIDE PANELS -
CAPACITY 15U - DIMENSIONS 758X600X450 MM - READY-
ASSEMBLED**

Emballage (nombre number of units)	1
Volume (dm ³)	219,296
Poids (g)	26 750,00

Caractéristiques du produit**Linkeo fix 19" cabinets****Fix side panels**

- Delivered ready-assembled
- Depth 450 mm
- Capacity : 15 U
- Height : 758 mm
- Width : 600 mm
- Loading capacity : 45 kg

Caractéristiques générales**Linkeo 19" and 10" wall-mounting cabinets**

- IP 20 - IK 08
- Equipped with:
 - 1 reversible door made of screen-printed safety glass and with integrated lock
 - 2 x 19" uprights with U marking and adjustable in depth
 - 3 pre-cut cable entries (top, bottom and rear). 1 brush for a cable entry. Top perforations for natural ventilation
 - panels with automatic grounding (ready assembled version)
 - earthing kit (flatpack version)
- Anthracite grey RAL 7016

Documentation associée**Catalogue pages & additional information**

- [Description page \(p.784\)](#)
- [Technical page \(p.790\)](#)
- [Technical page \(p.791\)](#)

**Installation & technical data**

- F02824EN-00

**Installation instructions & related documents**

- [LE10110AA-01](#)

REF . 6 462 03

Pièces détachées

REF.	DESIGNATION	PRIX UNITAIRE (€ HT*)	COMMANDE MINIMUM
981080	SET OF 2 HINGES FOR LINKEO WALLMOUNTING CABINET	5.84	1
981082	LOCKING KIT (BARREL AND KEY) FOR LINKEO DOOR	12.75	1
981083	SET OF 2 KEYS (CODE 9473) FOR LINKEO RAL7016 DOOR AND SIDE PANELS	5.84	1
981087	LINKEO RAL7016 COMPLETE DOOR 15UX19" (MOUNTED, FLATPACK AND PIVOTING VERSION)	86.74	1

Garantie des pièces détachées

Pas d'incidence sur la garantie du produit fini.

Pièces détachées garanties contre défaut par échange sous 15 jours maxi.