

CAT. N° 4 095 69



**MCB - DX<sup>3</sup> - 16 KA - DIRECT CURRENT - 12 V= TO 500 V= - 2P - 20 A**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,369
Weight (g)	296,00

### Product characteristics

#### Direct current circuit breakers

- Nominal rating  $I_n$  : 20 A
- Number of poles protected : 2
- Number of modules : 2

### General characteristics

#### MCBs DX<sup>3</sup> - 16 kA - direct current - thermal magnetic circuit breakers from 0.5 A to 63 A

- Operating voltage from 12 V= to 500 V=
- Breaking capacity
  - 16 kA - IEC 60947-2 - 250 V=
  - 10 kA - IEC 60947-2 - 440 V=
  - 6 kA - IEC 60947-2 - 500 V=
- Magnetic threshold from 5 to 7  $I_n$
- Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries and motorised controls

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.068\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

#### Installation & technical data

- [F01462EN/02](#)