

CAT. N° 4 098 04


**MCB - DX<sup>3</sup> - 25 KA - 1P - 230/400 V~ - 2 A - D CURVE**

|                           |        |
|---------------------------|--------|
| Pack (number of units)    | 1      |
| Volume (dm <sup>3</sup> ) | 0,229  |
| Weight (g)                | 150,00 |

**Product characteristics**
**Single pole 230/400 V~**

- D curve
- Nominal rating I<sub>n</sub> : 2 A
- Number of modules : 1

**General characteristics**
**MCBs DX<sup>3</sup> - 25 kA - thermal magnetic MCBs from 2 A to 125 A - C and D curves**

- Breaking capacity:
  - 25 kA - IEC 60947-2 - 400 V~
  - Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries and motorised controls

**Documentation**

**Catalogue pages & additional information**

- [Description page \(p.068\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)


**Agreements & certificates of conformity**

- [LOVAG - IT 13.030](#)