

CAT. N° 4 098 11


MCB - DX³ - 25 KA - 1P - 230/400 V~ - 40 A - D CURVE

Pack (number of units)	1
Volume (dm ³)	0,332
Weight (g)	242,00

Product characteristics
Single pole 230/400 V~

- D curve
- Nominal rating I_n : 40 A
- Number of modules : 1.5

General characteristics
MCBs DX³ - 25 kA - thermal magnetic MCBs from 2 A to 125 A - C and D curves

- Breaking capacity:
 - 25 kA - IEC 60947-2 - 400 V~
 - Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls

Documentation

Catalogue pages & additional information

- [Description page \(p.068\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)


Environmental product profile

- [Environnemental product sheet n°8 E0084A-FR](#)


Agreements & certificates of conformity

- [LOVAG - IT 13.030](#)