

CAT. N° 4 100 39


MCB - DX³ - 36 KA - 4P 400 V~ - 50 A - C CURVE

| | |
|---------------------------|--------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 1,04 |
| Weight (g) | 888,00 |

Product characteristics
4-pole - 400 V~

- C curve
- Nominal rating I_n : 50 A
- Number of modules : 6

General characteristics
MCBs DX³ - 36 kA - thermal magnetic MCBs from 10 A to 80 A - C curve

- Breaking capacity:
 - 36 kA - IEC 60947-2 - 400 V~
 - Can be equipped with DX³ auxiliaries and accessories

Documentation

Catalogue pages & additional information

- [Description page \(p.069\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)


Installation & technical data

- [F01218EN-00](#)


Environmental product profile

- [Environnemental product sheet n°8 E0084A-FR](#)


Installation instructions & related documents

- [LE03603AB](#)


Agreements & certificates of conformity

- [LOVAG - IT 13031](#)