

CAT. N° 4 090 90


MCB - DX³ 10000 - 16 KA - 4P 400 V~ - 100 A - B CURVE

Pack (number of units)	1
Volume (dm ³)	1,04
Weight (g)	925,00

Product characteristics
4-pole 400 V~

- B curve
- Nominal rating I_n : 100 A
- Number of modules : 6

General characteristics
MCBs DX³ 10000 - 16 kA - thermal magnetic circuit breakers from 1 A to 125 A - B and C curves

- Conform to IEC 60898-1
- Compatible with prong-type and fork type supply busbars (except 80 A, 100 A and 125 A MCBs)
- Breaking capacity
 - 10000 - IEC 60898-1 - 400 V~
 - 16 kA - IEC 60947-2 - 400 V~
- Can be equipped with DX³ signalling and remote tripping auxiliaries, motorised controls and add-on modules

Documentation

Catalogue pages & additional information

- [Description page \(p.066\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)


Installation & technical data

- [F01204EN-01](#)


Installation instructions & related documents

- [LE03603AB](#)


Environmental product profile

- [Environnemental product sheet n°8 E0084A-FR](#)