

CAT. N° 4 093 62


MCB - DX³ 10000 - 16 KA - 4P 400 V~ - 80 A - C CURVE


Pack (number of units)	1
Volume (dm ³)	1,04
Weight (g)	926,00

Product characteristics
4-pole 400 V~

- C curve
- Nominal rating I_n : 80 A
- Number of modules : 6

General characteristics
MCBs DX³ 10000 - 16 kA - thermal magnetic circuit breakers from 1 A to 125 A - B and C curves

- Conform to IEC 60898-1
- Compatible with prong-type and fork type supply busbars (except 80 A, 100 A and 125 A MCBs)
- Breaking capacity
 - 10000 - IEC 60898-1 - 400 V~
 - 16 kA - IEC 60947-2 - 400 V~
- Can be equipped with DX³ signalling and remote tripping auxiliaries, motorised controls and add-on modules

Documentation
 **Catalogue pages & additional information**

- [Description page \(p.066\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

 **Installation & technical data**

- [F01204EN-01](#)

 **Installation instructions & related documents**

- [LE03603AB](#)

 **Environmental product profile**

- [Environnemental product sheet n°8 E0084A-FR](#)