

CAT. N° 4 192 36

**MCB RX³ 6000 - 3P 400 V~ - 20 A - C CURVE - PRONG/FORK TYPE SUPPLY BUSBARS**

Pack (number of units)	4
Volume (dm ³)	2,694
Weight (g)	1 564,00

Product characteristics**3-pole 400 V~**

- C curve
- Nominal rating In : 20 A
- Number of modules : 3

General characteristics**MCBs RX³ 6000 - thermal magnetic MCBs from 6 A to 63 A - C curve**

- Conform to IEC 60898-1
- Do not accept auxiliaries, and add-on modules
- Compatible with prong-type supply busbars
- Breaking capacity:
 - 6000 - IEC 60898-1 - 230/400 V~
 - 6 kA - IEC 60947-2 - 230/400 V~
 - 10000 - IEC 60898-1 - 127/220 V~
 - 10 kA - IEC 60947-2 - 127/220 V~

Documentation**Catalogue pages & additional information**

- [Description page \(p.052\)](#)
- [Dimensions of din-rail equipment](#)

**Agreements & certificates of conformity**

- [OC / CB - IT-14270](#)
- [VDE - 40041249](#)
- [IMQ - IT-14270](#)

**Installation & technical data**

- [F01909EN-02](#)

**Environmental product profile**

- [Environnemental product sheet n°20 E0161B-EN](#)