

CAT. N° 4 198 86

**MCB RX³ 6000 - 3P 400 V~ - 25 A - C CURVE - PRONG-TYPE SUPPLY BUSBARS**


Pack (number of units)	4
Volume (dm ³)	1,864
Weight (g)	1 615,00

Product characteristics**3-pole 400 V~**

- C curve
- Nominal rating In : 25 A
- Number of modules : 3

General characteristics**MCBs RX³ 6000 - thermal magnetic MCBs from 6 A to 63 A - C curve**

- Conform to IEC 60898-1
- Do not accept auxiliaries, and add-on modules
- Compatible with prong-type supply busbars
- Breaking capacity:
 - 6000 - IEC 60898-1 - 230/400 V~
 - 6 kA - IEC 60947-2 - 230/400 V~
 - 10000 - IEC 60898-1 - 127/220 V~
 - 10 kA - IEC 60947-2 - 127/220 V~

Documentation **Catalogue pages & additional information**

- [Description page \(p.051\)](#)
- [Dimensions of din-rail equipment](#)

 **Agreements & certificates of conformity**

- [VDE - 40044431](#)
- [VDE - 40042228](#)
- [QC / CB - IT 16505](#)
- [SNI - PCS 00498.01](#)

 **Installation & technical data**

- [F01910EN-01](#)

 **Environmental product profile**

- [Environnemental product sheet n°20 E0162B-EN](#)