

CAT. N° 4 041 71


MCB TX³ 10000 - 1P - 230/400 V~ - 16 A - C CURVE


Pack (number of units)	10
Volume (dm ³)	1,619
Weight (g)	1 291,00

Product characteristics
Single pole 230/400 V~

- C curve
- Nominal rating I_n : 16 A
- Number of modules : 1

General characteristics
MCBs TX³ 10000 - thermal magnetic MCBs from 2 A to 63 A - B & C curve

- Conform to IEC 60898-1
- Compatible with prong-type and fork type supply busbars
- Equipped with special DIN rail clamp allowing independent MCB removal with supply busbar in place
- Breaking capacity:
 - 10000 - IEC 60898-1 - 230/400 V~
 - 10 kA - IEC 60947-2 - 230/400 V~
- Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls
- Do not accept add-on modules

Documentation
 **Catalogue pages & additional information**

- [Description page \(p.055\)](#)
- [Dimensions of din-rail equipment](#)

 **Agreements & certificates of conformity**

- [IMQ - IT-16157](#)
- [OC / CB - IT-15814](#)
- [VDE - 40042812](#)

 **Installation & technical data**

- [F01900EN-01](#)