

CAT. N° 4 035 21



## MCB TX<sup>3</sup> 6000 - 1P - 230/400 V~ - 2 A - C CURVE - PRONG/FORK TYPE SUPPLY BUSBARS

Pack (number of units)	5
Volume (dm <sup>3</sup> )	1,619
Weight (g)	1 296,00

### Product characteristics

#### 2-pole 230/400 V~

- C curve
- Nominal rating I<sub>n</sub> : 2 A
- Number of modules : 2

### General characteristics

#### MCBs TX<sup>3</sup> 6000 - thermal magnetic MCBs from 2 A to 63 A - B & C curve

- Conform to IEC 60898-1
- Compatible with prong-type and fork type supply busbars
- Equipped with special DIN rail clamp allowing independent MCB removal with supply busbar in place
- Breaking capacity:
  - 6000 - IEC 60898-1 - 230/400 V~
  - 6 kA - IEC 60947-2 - 230/400 V~
- Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries and motorised controls
- Do not accept add-on modules

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)



#### Agreements & certificates of conformity

- [VDE - 40042432](#)
- [OC / CB - IT-15813](#)
- [OC / CB - IT - 15108](#)



#### Installation & technical data

- [F01547EN/01](#)