

CAT. N° 4 035 26



MCB TX³ 6000 - 2P - 230/400 V~ - 10 A - C CURVE - PRONG/FORK TYPE SUPPLY BUSBARS

Pack (number of units)	5
Volume (dm ³)	1,619
Weight (g)	1 277,00

Product characteristics

2-pole 230/400 V~

- C curve
- Nominal rating I_n : 10 A
- Number of modules : 2

General characteristics

MCBs TX³ 6000 - thermal magnetic MCBs from 2 A to 63 A - B & C curve

- Conform to IEC 60898-1
- Compatible with prong-type and fork type supply busbars
- Equipped with special DIN rail clamp allowing independent MCB removal with supply busbar in place
- Breaking capacity:
 - 6000 - IEC 60898-1 - 230/400 V~
 - 6 kA - IEC 60947-2 - 230/400 V~
- Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls
- Do not accept add-on modules

Documentation



Catalogue pages & additional information

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)



Agreements & certificates of conformity

- [VDE - 40042432](#)
- [OC / CB - IT-15813](#)
- [OC / CB - IT - 15108](#)



Installation & technical data

- [F01547EN/01](#)