

CAT. N° 4 034 18

**MCB TX³ 6000 - 4P 400 V~ - 20 A - B CURVE**

Pack (number of units)	1
Volume (dm ³)	0,701
Weight (g)	528,00

Product characteristics**4-pole 400 V~**

- B curve
- Nominal rating I_n : 20 A
- Number of modules : 4

General characteristics**MCBs TX³ 6000 - thermal magnetic MCBs from 2 A to 63 A - B & C curve**

- Conform to IEC 60898-1
- Compatible with prong-type and fork type supply busbars
- Equipped with special DIN rail clamp allowing independent MCB removal with supply busbar in place
- Breaking capacity:
 - 6000 - IEC 60898-1 - 230/400 V~
 - 6 kA - IEC 60947-2 - 230/400 V~
- Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls
- Do not accept add-on modules

Documentation**Catalogue pages & additional information**

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)

**Agreements & certificates of conformity**

- VDE - 40042432
- OC / CB - IT-15813