

CAT. N° 0 270 18

**MCCB - DRX 125 - THERMAL MAGNETIC - ICU 10 KA - 415 V~ - 4P - IN 100 A**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,53
Weight (g)	1 113,00

**Product characteristics****DRX 125****Breaking capacity Icu 10 kA (415 V~)**

- 4P
- 100 A

**General characteristics****DRX™ 125 - thermal magnetic MCCBs from 15 to 125 A**

- For switching, control, isolation and protection of low-voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with:
  - M5 terminal for  $I_n \leq 50$  A and M8 range for  $I_n > 50$  A
  - Fixing screws
  - Insulating shields (2 for 3P and 3 for 4P)
- Fixed thermal and magnetic
- Conform to IEC 60947-2, in compliance with NEMA

**Documentation****Catalogue pages & additional information**

- [Description page \(p.127\)](#)
- [Technical page \(p.128\)](#)
- [DRXTM 125](#)

**Agreements & certificates of conformity**

- [OC / CB - SE 57100](#)