

CAT. N° 0 270 24



## MCCB - DRX 125 - THERMAL MAGNETIC - ICU 20 KA - 415 V~ - 3P - IN 40 A

Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,215
Weight (g)	836,00

### Product characteristics

#### DRX 125

#### Breaking capacity Icu 20 kA (415 V~)

- 3P
- 40 A

### General characteristics

#### DRX™ 125 - thermal magnetic MCCBs from 15 to 125 A

- For switching, control, isolation and protection of low-voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with:
  - M5 terminal for In ≤ 50 A and M8 range for In > 50 A
  - Fixing screws
  - Insulating shields (2 for 3P and 3 for 4P)
- Fixed thermal and magnetic
- Conform to IEC 60947-2, in compliance with NEMA

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.127\)](#)
- [Technical page \(p.128\)](#)
- [DRXTM 125](#)



#### Agreements & certificates of conformity

- [LOVAG - 06.001/003/005](#)
- [OC / CB - SE 57102](#)