

CAT. N° 0 270 42



## MCCB - DRX 125 - THERMAL MAGNETIC - ICU 25 KA - 220/240 V~ - 1P - 25 A

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,632
Weight (g)	345,00

### Product characteristics

#### DRX 125

#### Breaking capacity Icu 25 kA (220/240 V~)

- 1P
- Icu 25 kA (240 V~)
- 25 A

### General characteristics

#### DRX™ 125 - thermal magnetic MCCBs from 15 to 125 A

- For switching, control, isolation and protection of low-voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with:
  - M5 terminal for  $I_n \leq 50$  A and M8 range for  $I_n > 50$  A
  - Fixing screws
  - Insulating shields (2 for 3P and 3 for 4P)
- Fixed thermal and magnetic
- Conform to IEC 60947-2, in compliance with NEMA

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.127\)](#)
- [Technical page \(p.128\)](#)
- [DRXTM 125](#)