

CAT. N° 4 225 78



MCCB DPX³ 1600 - S1 ELECTRONIC RELEASE - 3P - ICU 100 KA (400 V~) - IN 1250 A

Pack (number of units)	1
Volume (dm ³)	47,6
Weight (g)	15 951,00

Product characteristics

MCCBs electronic release S1 fixed version

- Adjustment of I_r, I_{sd}
- Instantaneous protection I_f = 20 kA
- Green indicator lamp
- Connector for test unit
- Dynamic selectivity
- 4P version: adjustment of neutral on front panel

Breaking capacity I_{cu} 100 kA (400 V~)

- 3P
- I_n : 1250 A

General characteristics

DPX³ 1600 - S1 electronic release MCCBs from 630 to 1600 A

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Can be used with residual current relays
- Do not accept DPX³ electronic interface for Modbus Cat.No 4 210 75
- Supplied complete with:
 - connection plates for bars
 - insulated shields (phase barriers)
- Conform to IEC 60947-2 - Sealable adjustment
- Can be mounted on plate in XL³ cabinets and enclosures

Documentation

Catalogue pages & additional information

- [Description page \(p.150\)](#)
- [Technical page \(p.134-135\)](#)
- [DPX³ 160/250/630 & 1600](#)
- [DPX³ 1600](#)

Installation & technical data

- [F01964EN/01](#)