

CAT. N° 4 223 26



## MCCB DPX<sup>3</sup> 1600 - S2 ELECTRONIC RELEASE - 3P - Icu 70 KA (400 V~) - IN 1250 A

Pack (number of units)	1
Volume (dm <sup>3</sup> )	48
Weight (g)	15 925,00

### Product characteristics

#### MCCBs electronic release S2 fixed version

- Adjustment of Ir, Isd, tr, tsd
- Instantaneous protection If = 20 kA
- Green indicator lamp
- Connector for test unit
- Logic and dynamic selectivity

#### Breaking capacity Icu 70 kA (400 V~)

- 3P
- In : 1250 A

### General characteristics

#### DPX<sup>3</sup> 1600 - S2 electronic release MCCBs from 630 to 1600 A

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Can be used with residual current relays
- Supplied complete with:
  - connection plates for bars
  - insulated shields (phase barriers)
- Conform to IEC 60947-2 - Sealable adjustment
- Can be mounted on plate in XL<sup>3</sup> cabinets and enclosures

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.151\)](#)
- [Technical page \(p.134-135\)](#)
- [DPX<sup>3</sup> 160/250/630 & 1600](#)
- [DPX<sup>3</sup> 1600](#)

#### Installation & technical data

- [F01964EN/01](#)
- [MODBUS TABLE 14](#)

#### Installation instructions & related documents

- [LE07037AA](#)
- [LE07038AB](#)
- [LE08866AB](#)
- [LE08865AB](#)

#### Firmwares

- [Legrand Power Control Station software](#)