

CAT. N° 4 222 69



## MCCB DPX<sup>3</sup> 1600 - THERMAL MAGNETIC RELEASE - 4P - Icu 50 KA (400 V~) - IN 800 A

|                           |           |
|---------------------------|-----------|
| Pack (number of units)    | 1         |
| Volume (dm <sup>3</sup> ) | 48        |
| Weight (g)                | 17 432,00 |

### Product characteristics

#### MCCBs thermal magnetic release fixed version

- Thermal adjustable from 0.8 to 1 In
- Magnetic adjustable from 5 to 10 In

#### Breaking capacity Icu 50 kA (400 V~)

- 4P
- In : 800 A

### General characteristics

#### DPX<sup>3</sup> 1600 - thermal magnetic release MCCBs from 630 to 1250 A

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Can be used with residual current relays
- Supplied complete with:
  - connection plates for bars
  - insulated shields (phase barriers)
- Conform to IEC 60947-2 - Sealable adjustment
- Can be mounted on plate in XL<sup>3</sup> cabinets and enclosures

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.150\)](#)
- [Technical page \(p.134-135\)](#)
- [DPX<sup>3</sup> 160/250/630 & 1600](#)
- [DPX<sup>3</sup> 1600](#)

#### Installation & technical data

- [F01963EN01DPX3\\_1600MT\\_ENGv5](#)

#### Installation instructions & related documents

- [LE07037AA](#)