

CAT. N° 4 225 03



MCCB DPX³ 630 - S1 ELECTRONIC RELEASE - 4P - Icu 36 KA (400 V~) - IN 250 A

Pack (number of units)	1
Volume (dm ³)	9,214
Weight (g)	7 570,00

Product characteristics

MCCBs electronic release S1 - fixed version

- Adjustment of Ir, Isd
- Instantaneous protection If = 5 kA
- Green indicator lamp
- Connector for test unit
- Dynamic selectivity
- 4P version: adjustment of neutral on front panel

Breaking capacity Icu 36 kA (400 V~)

- 4P
- In : 250 A

General characteristics

DPX³ 630 - S1 electronic release MCCBs from 250 to 630 A

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Can be used with earth leakage modules or with residual current relays
- Do not accept DPX³ electronic interface for Modbus Cat.No 4 210 75
- Supplied complete with:
 - fixing screws
 - connection plates for bars
 - insulated shields (phase barriers)
- Conform to IEC 60947-2 - Sealable adjustment
- Can be mounted on plate in XL³ cabinets and enclosures

Documentation

Catalogue pages & additional information

- [Description page \(p.145\)](#)
- [Technical page \(p.134-135\)](#)
- [DPX³ 160/250/630 & 1600](#)
- [DPX³ 630](#)

Installation & technical data

- [LE08011AA](#)
- [F01959EN/02](#)