

CAT. N° 3 381 13



METAL DOOR FOR XL³ S 4000 DISTRIBUTION ENCLOSURES HEIGHT 2200 MM AND WIDTH 800 MM - SUPPLIED WITH FIXED HANDLE

| | |
|---------------------------|-----------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 174,857 |
| Weight (g) | 26 144,00 |

Product characteristics

Metal doors

- Supplied with fixed handle

Height 2200 mm

- For enclosure width : 800 mm

General characteristics

XL³ S 4000 - distribution enclosures and equipment

- Doors, side or rear panels, supports for faceplates and functional uprights, to be ordered separately
- Enclosures supplied with corner pieces for plinth
- Take protection devices up to 4000 A
- Used to create assemblies certified IEC 61439-2
- IP 30 without door
- IP 40 with door
- External height 2000 or 2200 mm
- Capacity 16 modules/row (424 mm wide enclosures), 24 modules/row (574 mm or 800 mm wide enclosures with internal cable sleeve), 36 modules/row (774 mm wide enclosures)
- Usable faceplate height 1800 mm or 2000 mm

Documentation

Catalogue pages & additional information

- [Description page \(p.246\)](#)
- [Technical page \(p.255\)](#)

Agreements & certificates of conformity

- [LOVAG - IT 18.039](#)
- [LOVAG - IT 17.096](#)
- [LOVAG - IT 18.038](#)
- [LOVAG - IT 18.047](#)
- [LOVAG - IT 18.118](#)
- [LOVAG - IT 18.001](#)

Installation instructions & related documents

- [LE09702AB](#)