

CAT. N° 0 300 15


MINI-TRUNKING DLPLUS - 32X12.5 MM - WITHOUT PARTITION - L 2.1 M - WHITE

Pack (number of metres)	80
Volume (dm ³)	40
Weight (g)	13 800,00

Product characteristics

Mini-trunking

- EN 50085-2-1 approved

Without central partition

- Mini-trunking with cable grip
- Equipped with an integrated device for holding cables in place
- Length 2.10 m
- 32 x 12.5
- Without adhesive

General characteristics

DLPlus mini-trunking 20 x 12.5 and 32 x 12.5 - profiles and finishing accessories

Documentation


Catalogue pages & additional information

- [Selection chart \(p.796\)](#)
- [Description page \(p.798\)](#)
- [DLPlus mini-trunking](#)


Environmental product profile

- [Environnemental product sheet n°6 E7066B-EN](#)


Agreements & certificates of conformity

- [NF 004 - NF 593021O](#)