

CAT. N° 0 300 27



MINI-TRUNKING DLPLUS - 40X20 MM - WITHOUT PARTITION - L 2.1 M - WHITE

Pack (number of metres)	48
Volume (dm ³)	48
Weight (g)	15 600,00

Product characteristics

Mini-trunking with cable grip

- EN 50085-2-1 approved
- Equipped with an integrated device for holding cables in place

Without central partition

- Length 2.10 m
- 40 x 20
- Without adhesive

General characteristics

DLPlus mini-trunking 32 x 16 and 40 x 20 - profiles and finishing accessories

Documentation



Catalogue pages & additional information

- [Selection chart \(p.796\)](#)
- [Description page \(p.799\)](#)
- [DLPlus mini-trunking](#)



Environmental product profile

- Environmental product sheet n°6 E7066B-EN



Agreements & certificates of conformity

- [NF 004 - NF 593021O](#)