

CAT. N° 5 556 09

**MOBILE SOCKET P17 PRO - IP66/67 - 380/415 V~ - 125 A - 3P+N+E**

|                           |          |
|---------------------------|----------|
| Pack (number of units)    | 1        |
| Volume (dm <sup>3</sup> ) | 7,88     |
| Weight (g)                | 1 680,00 |

## Product characteristics

**Mobile sockets****380/415 V~**

- 125 A
- 3P+N+E

## General characteristics

**P 17 Tempra Pro IP 66/67 LV 63 and 125 A**

## Documentation

**Catalogue pages & additional information**

- [Selection chart \(p.381\)](#)

**Agreements & certificates of conformity**

- [OC / CB - FR\\_706516](#)
- [CCC - CQC2018010203055870](#)

**Installation & technical data**

- [F02385EN-01](#)

**Environmental product profile**

- [Environnemental product sheet n°9 E0060B-EN](#)