

CAT. N° 0 048 88



MONOBLOC MODULAR DISTRIBUTION BLOCK - 4P - 125 A - 15 CONNECTIONS

Pack (number of units)	5
Volume (dm ³)	4,459
Weight (g)	2 181,00

Product characteristics

Monobloc modular distribution blocks

- Mounting on rail or on plate with 2 screws
- Supplied with insulated back plate and transparent protective front cover
- Each bar can be labelled using CAB 3
- Possible to add IP 2X terminal block

Four pole

- Equipped with 4 bars
- With short ferrule supplied for flexible connection 25 mm²
- Rating : 125 A
- Isc peak : 14.5 kA
- Icw : 4.2 kA
- Number of modules : 8

General characteristics

Modular distribution blocks 40 to 250 A

- Standard distribution
- Connection with or without Starfix ferrules
- Self-extinguishing, according to EN 60695-2-11: 960 °C on active part supports

Documentation



Catalogue pages & additional information

- [Selection chart \(p.198\)](#)
- [Description page \(p.201\)](#)
- [Modular distribution blocks](#)