

CAT. N° 0 779 01



MOSAIC NON MANAGEABLE SWITCH - 10/100 BASE T - POE SUPPLY - 6 MODULES - WHITE

Pack (number of units)	1
Volume (dm ³)	1,02
Weight (g)	237,00

Product characteristics

Flush-mounting Ethernet 10/100 base T switches

- For networking computer peripherals without a patch panel: computers, printers, servers, etc.
- Possibility of extending an existing network by simply replacing an RJ 45 socket
- Toolless connection
- Compliant with IEEE 802.3 (Ethernet) and EN 50081/82-2 (EMC requirements) standards
- Can be installed in any support with minimum 40 mm depth
- 6 ports on front + 1 side RJ 45 connector for cabling and carrying out link tests
- Port status display integrated into the RJ 45 connectors
- Labelling of each port from 1 to 6 and marker holder for switch identification
- 6 modules

Non-manageable PoE power supply (802.3 af) - Mosaic

- White

General characteristics

Legrand cabling system, LCS³ - PoE switches and injectors

Documentation

Catalogue pages & additional information

- [Description page \(p.893\)](#)
- [Description page \(p.80\)](#)
- [Technical page \(p.111\)](#)
- [Technical page \(p.114\)](#)

Installation instructions & related documents

- [LE02979AA](#)