

REF . 4 173 20

**MPCB MPX³ 32H - THERMAL MAGNETIC - MOTOR PROTECTION - 3P - 0.16 A - 100 KA**

Emballage (nombre number of units)	1
Volume (dm ³)	0,53
Poids (g)	360,00

Caractéristiques du produit**Thermal magnetic MPCBs**

- Adjustable thermal release
- Magnetic release 13 le max.

MPX³ 32H

- High breaking capacity
- With rotary handle
- Fixing on rail
- 3-phase motor 400/415 V : 0.02 kW
- Thermal release adjustment range : 0.1 to 0.16 A
- Magnetic release operating current : 2.1 A
- 415 V breaking capacity Icu : 100 kA

Caractéristiques générales**MPCBs MPX³ - motor protection circuit breakers from 0.16 A to 100 A**

- Conform to IEC 60947-1, IEC 60947-2, IEC 60947-4 ; class 10

Documentation associée**Catalogue pages & additional information**

- [Description page \(p.184\)](#)
- [Technical page \(p.182-183\)](#)
- [MPCBs MPX3](#)

**Installation & technical data**

- [F01988EN-05](#)

**Installation instructions & related documents**

- [LE07207AB](#)

**Environmental product profile**

- [Environnemental product sheet n°8 E0083A-EN](#)