

CAT. N° 4 173 01



MPCB MPX³ 32S - THERMAL MAGNETIC - MOTOR PROTECTION - 3P - 0.25 A - 100 KA

Pack (number of units)	1
Volume (dm ³)	0,499
Weight (g)	315,00

Product characteristics

Thermal magnetic MPCBs

- Adjustable thermal release
- Magnetic release 13 Ie max.

MPX³ 32S

- Standard breaking capacity
- With toggle handle
- Fixing on rail
- 3-phase motor 400/415 V : 0.06 kW
- Thermal release adjustment range : 0.16 to 0.25 A
- Magnetic release operating current : 3.3 A
- 415 V breaking capacity Icu : 100 kA

General characteristics

MPCBs MPX³ - motor protection circuit breakers from 0.16 A to 100 A

- Conform to IEC 60947-1, IEC 60947-2, IEC 60947-4 ; class 10

Documentation



Catalogue pages & additional information

- [Description page \(p.184\)](#)
- [Technical page \(p.182-183\)](#)
- [MPCBs MPX3](#)



Installation & technical data

- [F01988EN-05](#)



Installation instructions & related documents

- [LE07207AB](#)



Environmental product profile

- [Environnemental product sheet n°8 E0083A-EN](#)