

CAT. N° 0 026 71



MULTIFUNCTION REMOTE CONTROL DIMMER - FOR DIMMABLE LEDs AND CFLS - 1 MODULE

Pack (number of units)	1
Volume (dm ³)	0,198
Weight (g)	75,00

Product characteristics

Multifunction remote control dimmer 240 V~ 50/60Hz

- Symmetrical rail mounting
- Compatible with energy saving lamps: dimmable LEDs and CFLs (Compact Fluorescent Lamps)
- Load:
 - 1 to 75 W dimmable LEDs
 - 1 to 100 W dimmable CFL
 - 1 to 300 VA dimmable fluorescent tubes
 - 1 to 200 VA dimmable LED / halogen lamps with ferromagnetic transformer
 - 1 to 200 VA dimmable LED / halogen lamps with electronic transformer
 - 1 to 300 W halogen and incandescent lamps
- 5 manually programmable functions: dimmer with level memory, dimmer without level memory, latching relay, timer, dual threshold timer.
- 3 additional functions accessible via Legrand NFC Close UP application only: child room fading, timer with switch-off warning function, dimming at preset levels.
- Remote control with non-illuminated pushbutton
- Can replace a pre-installed dimmer,
- actuator or timer controlled by pushbuttons
- Power consumption in standby mode: 0.1 W
- Number of modules : 1

General characteristics

Lighting management remote control dimmers

Documentation

Catalogue pages & additional information

- [Description page \(p.094\)](#)
- [Dimensions of din-rail equipment](#)
- [Light sensitive switches](#)

Installation & technical data

- [S000090635EN-3](#)

Installation instructions & related documents

- [LE08218AD](#)