

CAT. N° 4 130 68



OTO - FTTH PREWIRED/PRETERMINATED - 4 OF - 4 SC/APC FEEDTHROUGHS - 25 M CABLE

Pack (number of units)	1
Volume (dm ³)	4,249
Weight (g)	881,00

Product characteristics

Optical telecommunications outlet (OTO) - prewired and preterminated

- The OTO is the termination point of the FTTH installation in the home
- It is fixed in the home network cabinet and enables connection to the operator router
- The prewired and preterminated version enables direct connection to the BEP via the connectors for tool-free mounting on-site
- The pulling cord makes it easy to use in the riser and in conduits (Ø20 mm recommended)
- Technical characteristics:
 - For fixing on DIN rail or wall
 - Preterminated at both ends
 - G657A2 900 µm
 - Cable diameter: 4.2 mm
 - Pulling cord diameter: 13 mm

Prewired and preterminated OTO - 4 OF

- OTO with 4 SC/APC feedthroughs + 25 m of cable preterminated at both ends

General characteristics

Ftth - Fibre to the Home - preterminated solution

- The preterminated solution has been specially designed for make FttH available to all installers
- It requires no special equipment (does not require a device for slicing the fibre)
- It is recommended for buildings of average height (up to 12 apartments)

Documentation



Catalogue pages & additional information

- [Description page \(p.406\)](#)
- [Technical page \(p.407\)](#)



Installation instructions & related documents

- [LE06278AE](#)