

CAT. N° 0 778 78



OUTDOOR BACKLIT CODED KEYPAD WITH PUSH-BUTTON SOLIROC- FLUSH-MOUNTING -IK10-IP55

Pack (number of units)	1
Volume (dm ³)	1,619
Weight (g)	979,00

Product characteristics

Outdoor flush-mounting readers - IK 10 - IP 55

- Power supply 12/24 V DC/~

Backlit coded keypad with push-button

- Consumption: 75 mA at 12 VDC
- 1 relay output for door release or electromagnetic lock
- 1 push-button input for internal unlocking
- 1 push-button on the front panel for call, chime or door opening
- Up to 99 users

General characteristics

Soliroc™ - control mechanisms IK 10

- Suitable for public buildings, unsupervised passageways, car parks, communal areas in buildings
- High resistance to IK 10 impacts and humidity
- 4 fixing points by plugging the plate directly on the wall and 4 blanking plates to be force-mounted on the plate (can only be removed by drilling)
- Mechanisms supplied with cover plates, to be equipped with support frames and plates

Documentation



Catalogue pages & additional information

- [Description page \(p.611\)](#)



Installation instructions & related documents

- [LE03162AF](#)