

CAT. N° 5 552 85



PANEL MOUNTING SOCKET P17 - INCLINED OUTLET - IP44 - 200/250 V~ - 32 A - 3P+E

Pack (number of units)	5
Volume (dm ³)	5,867
Weight (g)	934,00

Product characteristics

Panel mounting sockets inclined outlet

- Can be fixed on plain faceplates or pre-drilled and on flush mounting boxes

200/250 V~

- IP 44
- 32 A
- 3P+E

General characteristics

P 17 Tempra Pro IP 44 - LV 16 and 32 A - sockets, plugs, mobile sockets, appliance inlets and interlocked switched sockets

Documentation

Catalogue pages & additional information

- [Selection chart \(p.380\)](#)
- [Description page \(p.382\)](#)
- [P 17 Tempra Pro](#)

Installation & technical data

- [F01811EN-03](#)

Installation instructions & related documents

- [LE05815AA-01](#)

Agreements & certificates of conformity

- [IMQ - CA02_05951](#)
- [CCC - CQC2016010203837678](#)
- [OC / CB - FR 641754/A1](#)