

CAT. N° 0 778 53



PLATE SOLIROC - 3 GANG - 110 X 252 MM - HORIZONTAL OR VERTICAL - IK10

Pack (number of units)	1
Volume (dm ³)	2,35
Weight (g)	475,00

Product characteristics

Plates - IK 10

- 3-gang plate
- 110 x 252 mm
- Horizontal or vertical mounting
- 71 mm fixing centres

General characteristics

Soliroc™ - sockets and mounting accessories IK 10

- Suitable for public buildings, unsupervised passageways, car parks, communal areas in buildings
- High resistance to IK 10 impacts and humidity
- 4 fixing points by plugging the plate directly on the wall and 4 blanking plates to be force-mounted on the plate (can only be removed by drilling)
- Mechanisms supplied complete with cover plates

Documentation

Catalogue pages & additional information

- [Description page \(p.612\)](#)
- [Technical page \(p.616-617\)](#)

Installation & technical data

- F00862EN-05

Installation instructions & related documents

- [LE01029AD](#)

Agreements & certificates of conformity

- NF - NF012_1023
- NF - NF012_1362
- OC / CB - FR_700177/A1
- OC / CB - 569889/A1
- OC / CB - FR_701873
- OC / CB - 619737
- OC / CB - FR_707077