

CAT. N° 1 371 78



## PRACTIBOX S FLUSH-MOUNTING CABINET FOR DRY PARTITION EARTH + NEUTRAL TERMINAL BLOCKS -SMOKED DOOR -3 ROWS 18 MODULES/ROW

Pack (number of units)	1
Volume (dm <sup>3</sup> )	31,366
Weight (g)	3 266,00

### Product characteristics

#### Cabinets supplied with earth and neutral terminal blocks

- Smoked Transparent door
- Number of rows : 3
- Number of modules per row : 18
- Total number of modules : 54
- Height : 615 mm
- Width : 436 mm
- Depth : 103 mm

### General characteristics

#### Practibox S - flush-mounting cabinets for dry partitions from 4 to 72 modules

- Allows to achieve assemblies conform to IEC 61439-3
- IP40 IK07
- Class II
- Plastic material
- Supplied with door
- For dry partitions
- 850° fireproof flush-mounting plastic boxes

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.217\)](#)
- [Technical page \(p.219\)](#)

#### Agreements & certificates of conformity

- [LOVAG - IT 18.173](#)
- [QC / CB - FR\\_703887/M1](#)

#### Installation & technical data

- [F02633EN-01](#)

#### Environmental product profile

- [Environnemental product sheet n°A E4067A-EN](#)