

CAT. N° 1 351 64



**PRACTIBOX S FLUSH-MOUNTING CABINET FOR DRY PARTITION -EARTH + NEUTRAL TERMINAL BLOCKS -WHITE DOOR -4 ROWS 12 MODULES/ROW**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	29,477
Weight (g)	3 116,00

**Product characteristics**

**Cabinets supplied with earth and neutral terminal blocks**

- White door
- Number of rows : 4
- Number of modules per row : 12
- Total number of modules : 48
- Height : 765 mm
- Width : 328 mm
- Depth : 103 mm

**General characteristics**

**Practibox S - flush-mounting cabinets for dry partitions from 4 to 72 modules**

- Allows to achieve assemblies conform to IEC 61439-3
- IP40 IK07
- Class II
- Plastic material
- Supplied with door
- For dry partitions
- 850° fireproof flush-mounting plastic boxes

**Documentation**

**Catalogue pages & additional information**

- [Description page \(p.217\)](#)
- [Technical page \(p.219\)](#)

**Installation & technical data**

- [F02633EN-01](#)

**Environmental product profile**

- [Environnemental product sheet n°A E4060A-EN](#)

**Installation instructions & related documents**

- [LE10835AA\\_05](#)

**Agreements & certificates of conformity**

- [LOVAG - IT 18.173](#)
- [OC / CB - FR\\_703887/M1](#)