

CAT. N° 1 350 34



PRACTIBOX S FLUSH-MOUNTING CABINET FOR DRY PARTITION WITHOUT TERMINAL BLOCKS - SMOKED DOOR - 4 ROWS - 12 MODULES PER ROW

Pack (number of units)	1
Volume (dm ³)	29,477
Weight (g)	2 850,00

Product characteristics

Cabinets supplied without terminal blocks

- Smoked Transparent door
- Number of rows : 4
- Number of modules per row : 12
- Total number of modules : 48
- Height : 765 mm
- Width : 328 mm
- Depth : 103 mm

General characteristics

Practibox S - flush-mounting cabinets for dry partitions from 4 to 72 modules

- Allows to achieve assemblies conform to IEC 61439-3
- IP40 IK07
- Class II
- Plastic material
- Supplied with door
- For dry partitions
- 850° fireproof flush-mounting plastic boxes

Documentation

Catalogue pages & additional information

- [Description page \(p.217\)](#)
- [Technical page \(p.219\)](#)

Installation & technical data

- [F02564EN-02](#)

Environmental product profile

- [Environnemental product sheet n°A E4067A-EN](#)

Installation instructions & related documents

- [LE10835AA_05](#)

Agreements & certificates of conformity

- [LOVAG - IT 18.173](#)
- [OC / CB - FR_703887/M1](#)