

CAT. N° 6 174 31

**PUSH ON/OFF AND ROTARY DIMMER BELANKO
COLOURS - 1000 W RL - 1 GANG - 2-WAY - BROWN**

Pack (number of units)	1
Volume (dm ³)	0,602
Weight (g)	174,00

Product characteristics**Dimmers****1000 W RL dimmer**

- Push on/off and rotary dimmer - 50/60 Hz
- 1 gang - 2-way
- 60-1000 W (230 V) / 60-500 W (127 V) for incandescent and halogen lamps
- 60-600 VA (230 V) / 60-300 VA (127 V) for halogen lamps with electronic transformer with leading edge behaviour
- 60-1000 VA (230 V) / 60-500 VA (127 V) for halogen lamps with ferromagnetic transformers
- Slider at the back to select 230 V or 127 V
- Brown

General characteristics**Belanko™ colours - Dimmers**

- Material: Thermoplastic with glossy satin finish
- Dimensions: 86 x 86 x 9.5 mm (1 gang) / 86 x 146 x 9.5 mm (2 gang)
- Supplied with 2 screws M3.5 for BS boxes

Documentation**Catalogue pages & additional information**

- [Description page \(p.555\)](#)

**Installation & technical data**

- F02401EN/00