

REF . 4 111 21



RCBO - DX³ 6000 - 6 KA - 1P+N 230 V~ - 6 A - 10 MA - A
TYPE - N LEFT HAND



Emballage (nombre number of units)	1
Volume (dm ³)	0,259
Poids (g)	146,00

Caractéristiques du produit

Single pole + neutral - 230 V~

- Neutral on left-hand side

A Type 10 mA

- C curve
- Nominal rating In : 6 A
- Number of modules : 1

Caractéristiques générales

RCBOs DX³ 6000 - 6 kA - residual current circuit breakers from 6 A to 32 A - A type

- Conform to IEC 61009-1
- Compatible with prong-type supply busbars
- Voltage dependent tripping
- Breaking capacity:
 - 6000 - IEC 61009-1 - 6 kA / IEC 60947-2 for single pole + neutral
- A type : detect AC and DC component faults
- Enhanced immunity to unwanted tripping in disturbed environments
- Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls

Documentation associée



Catalogue pages & additional information

- [Description page \(p.060\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)



Installation & technical data

- [F02071EN/01](#)



Installation instructions & related documents

- [LE09580AA](#)



Agreements & certificates of conformity

- [OC / CB - 689349/A1](#)