

CAT. N° 4 115 09


RCCB TX³ - 2P 230 V~ - 30 MA - 25 A - AC TYPE


| | |
|---------------------------|--------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 0,39 |
| Weight (g) | 201,00 |

Product characteristics
2-pole - 230 V~
AC type

- Sensitivity : 30 mA
- In : 25 A
- Number of modules : 2

General characteristics
RCCBs TX³ residual current circuit breakers - from 16 A to 80 A - AC and A types

- Conform to IEC 61008-1
- Compatible with prong-type and fork type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults

Documentation
 **Catalogue pages & additional information**

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)

 **Agreements & certificates of conformity**

- [VDE - 40041193](#)
- [OC / CB - CB FR_700536](#)
- [OC / CB - CB FR_704741](#)
- [VDE - 40041193](#)

 **Installation & technical data**

- [F01575EN/02](#)