

CAT. N° 4 030 40

**RCCB TX³ - 2P 230 V~ - 300 mA - 63 A - AC TYPE - DO NOT ACCEPT AUXILIARIES**

Pack (number of units)	1
Volume (dm ³)	0,367
Weight (g)	198,00

Product characteristics**2-pole - 230 V~****AC type**

- Sensitivity : 300 mA
- In : 63 A
- Number of modules : 2

General characteristics**RCCBs TX³ - residual current circuit breakers - from 25 A to 63 A - AC and A types**

- Conform to IEC 61008-1
- Compatible with prong-type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults
- Do not accept auxiliaries

Documentation **Catalogue pages & additional information**

- [Description page \(p.053\)](#)
- [Dimensions of din-rail equipment](#)

 **Agreements & certificates of conformity**

- [OC / CB - CB FR_700536](#)
- [OC / CB - CB FR_704741](#)
- [VDE - 40036431](#)
- [VDE - 40036431](#)

 **Installation & technical data**

- [F01540EN/02](#)