

CAT. N° 4 020 64


RCD LR - 4P 400 V~ - 63 A - 30 MA - AC TYPE

Pack (number of units)	1
Volume (dm ³)	0,701
Weight (g)	377,00

Product characteristics
4-pole - 400 V~ - neutral on right-hand side
AC type

- Sensitivity : 30 mA
- In : 63 A
- Number of modules : 4

General characteristics
RCCBs RX³ - residual current circuit breakers from 25 A to 63 A - AC and A types

- Conform to IEC 61008-1
- AC type : detect AC component faults
- A type : detect AC and DC component faults
- Compatible with prong-type and fork type supply busbars
- Do not accept auxiliaries

Documentation
 **Catalogue pages & additional information**

- [Description page \(p.050\)](#)
- [Dimensions of din-rail equipment](#)

 **Environmental product profile**

- [Environnemental product sheet n°8 E0013C-EN](#)

 **Agreements & certificates of conformity**

- [OC / CB - CB FR_705078](#)
- [OC / CB - CB-FR_700757](#)
- [VDE - 40034493](#)
- [VDE - 40034493](#)