


CAT. N° 0 205 41



## REAR AND SIDE PANELS XL<sup>3</sup> 4000 - HEIGHT 2000 MM - WIDTH 475 MM

Pack (number of units)	1
Volume (dm <sup>3</sup> )	34
Weight (g)	11 871,00

### Product characteristics

#### Enclosures and cable sleeves modular metal

##### Finishing panels IP 30

- Width 475 mm
- Height : 2000 mm

### General characteristics

#### Distribution enclosures XL<sup>3</sup> 4000

- IP 30 - IK 07
- IP 55 - IK 08 with door and sealing kit for use when joining enclosures
- Consist of the combination of a "roof-base" assembly, structural uprights, functional uprights, rear and side panels RAL 7035, plinths RAL 7004
- Height 2000 or 2200 mm.
- Capacity 24 modules (enclosures width 725 or width 975 with internal cable sleeve), 36 modules (enclosures width 975)
- Usable faceplate height 1800 mm (1700 mm only if using the pivoting support frame) or 2000 mm

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.266\)](#)
- [Technical page \(p.267\)](#)
- [Selection chart \(p.268\)](#)
- [XL3 4000 equipment for mounting on adjustable plates](#)

#### Agreements & certificates of conformity

- [LOVAG - IT 12.019](#)
- [LOVAG - IT 12.017](#)
- [LOVAG - IT 12.019](#)