

CAT. N° 0 036 71



REMOTE CONTROL DIMMER - FOR INCANDESCENT/HALOGEN LAMP - 6 MODULES

Pack (number of units)	1
Volume (dm ³)	1,315
Weight (g)	437,00

Product characteristics

Remote control dimmers 100 - 240 V~ - 50/60 Hz

Controlled via BUS line

- Symmetrical rail mounting
- Direct or remote control (switching and dimming) with non-illuminated double push-buttons or bus peripherals (Mosaic Programme and Céliane Programme)
- Equipped with illuminated scale indicating the light level of controlled lamps
- For incandescent and halogen lamps 230 V~, ELV halogen lamps with ferromagnetic or electronic transformers
- Load: 1000 W (for 230 V~ 50/60 Hz)
- Number of modules : 6

General characteristics

Lighting management remote control dimmers

Documentation



Catalogue pages & additional information

- [Description page \(p.094\)](#)
- [Dimensions of din-rail equipment](#)
- [Light sensitive switches](#)



Installation instructions & related documents

- [0064JR3/02_EN](#)