

CAT. N° 8 331 51



## ROTARY UNIVERSAL DIMMER SYNERGY - 1 GANG - 5 W/300 W- AUTHENTIC BRUSHED STAINLESS STEEL

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,677
Weight (g)	259,00

### Product characteristics

#### Push on/off rotary universal dimmers 5 W / 300 W

##### 1 gang

- Conform to IEC 60669-2-1
- For flush mounting back box to be min. 40 mm deep
- Equipped with overvoltage and short-circuit protection
- Screw terminals
- For all types of lamps:
  - dimmable LEDs: 5 W to 75W
  - dimmable compact fluorescent lamps: 5 W to 75 W
  - halogen with ferromagnetic or electronic transformer: 5 VA to 300 VA
  - fluorescent tube - ballast: 5 VA to 300 VA
  - halogen and incandescent 230 V: 5 W to 300 W
- When switched on, gradually (2 seconds) lights up at the level set before last switch-off
- Nominal plate dimensions: 86 x 86 mm
- Can be associated with an active power compensator
- Brushed stainless steel

### General characteristics

#### Synergy™ - single pole switches and dimmers - Authentic

- Slim front plate:
  - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
  - PSS: Plates made of Stainless Steel + rust resistance
  - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.585\)](#)



#### Installation & technical data

- [F02302EN-00](#)